




Deblocking

DTS m^odulo

AUTOMATED DEBLOCKING AND TAPE-STRIPPING,
INTELLIGENTLY COMBINED



Fascination for Innovation



The lenses are prepared for deblocking in a hot water bath.



The design allows for deblocking and tape-stripping of two lenses at the same time.



Block pieces are sorted automatically and prepared for quick reuse in the CCB Modulo blocker.

Benefits

- Fully automated deblocking and tape-stripping in one unit
- Automated cleaning and sorting of block pieces
- Highest throughput
- Lowest danger of lens breakage
- Easy plug & play installation
- Low maintenance



Smart deblocking
for environmentally friendly
alloy-free blocked lenses.



Integrated solution
Fully automated deblocking
and tape-stripping in one unit.



**Fully automated
efficient cleaning**
and sorting of block pieces
for reuse.

DTS modulo

Designed as a perfect supplement to the CCB Modulo, the DTS Modulo provides a smooth and efficient technology for deblocking and tape-stripping of two lenses simultaneously. After pretreatment, the fast handling system transfers the lenses into the working chamber. The Eco Fuse Technology (EFT) layer is removed with warm water thus separating the lenses safely and very fast from the block pieces without any residue.

In the following process step the tape is removed without the danger of lens breakage. The block pieces are sorted in boxes and prepared for quick reuse in the CCB Modulo, guaranteeing maximum ease of use. The tape and EFT material are collected using a band filter system and can be disposed of easily.

Suitable for all lens materials, the DTS Modulo is the optimal choice to meet the demands of mid- and high-performance labs.

technical data

lens diameter	up to ø 85 mm
lens material	all organic materials
power consumption	10 kVA avg.
air requirement	min. 6 bar (87 psi)
weight machine	approx. 420 kg (926 lb.)
dimensions (width x depth x height)	approx. 1750 x 1800 x 1715 mm (69 x 71 x 68 inches)

All data subject to change without notice. Please verify details with SCHNEIDER.

SCHNEIDER GmbH & Co. KG
Biegenstrasse 8-12
35112 Fronhausen
Germany
Phone: +49 (64 26) 96 96-0
Fax: +49 (64 26) 96 96-100
www.schneider-om.com
info@schneider-om.com


SCHNEIDER Optical Machines Inc.
6644 All Stars Avenue, Suite 100
Frisco, TX 75033, USA
Phone: +1 (972) 247-4000
Fax: +1 (972) 247-4060
info-us@schneider-om.com

SCHNEIDER Optical Machines
do Brasil Ltda.
Avenida Tucunaré, 574
Cond. Palmar Modular – Modulo 1
Tamboré
06460-020 Barueri – SP
Brazil
Phone: +55 (11) 4777-1717
info-brasil@schneider-om.com

SCHNEIDER Optical Machines
(Shanghai) Co., Ltd.
Room 202, 2nd Floor, Building 16
481 Guiping Road
200233 Shanghai – Xuhui District
Phone: +86 (21) 61 48 00 61-120
Fax: +86 (21) 61 48 00 65
info-cn@schneider-om.com

SCHNEIDER Optical Machines
Asia-Pacific Co., Ltd.
Piya Place Lunguan Building
29/1, Tower B, 9th Floor, Unit 9B
Soi Lunguan Ploenchit Road
Lumpini, Pathumwan
Bangkok 10330, Thailand
Phone: +66 (0) 2014-4690-2
Fax: +66 (0) 2014-4693
info-asia@schneider-om.com

For a complete list of SCHNEIDER agencies, please visit www.schneider-om.com



Fascination for Innovation